

Datasheet

SFRS14 monoclonal antibody (M01), clone 3C5

Alternatively spliced transcript variants have been described. [provided by RefSeq]

Catalog Number: H00010147-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant SFRS14.

Clone Name: 3C5

Immunogen: SFRS14 (NP_055699, 579 a.a. ~ 674 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

PQRADHRVVGTTIDQLVKRVIEGSLSPKERTLLKEDPAY
WFLSDENSLEYKYYKLKLAEMQRMSSENLRGADQKPT
SADCAVRAMLYSRAVRNLKKKL

Host: Mouse

Reactivity: Human

Applications: ELISA, IF, IHC-P, S-ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10147

Gene Symbol: SFRS14

Gene Alias: DKFZp779L2418

Gene Summary: This gene encodes a member of the arginine/serine-rich family of splicing factors. The encoded protein functions in mRNA processing.