

Name:CCDC93 mouse monoclonal antibody,clone 2H4
Product Data Sheet - TRUEMAB**Catalog: TA800598**

Components:	<ul style="list-style-type: none">• CCDC93 mouse monoclonal antibody,clone 2H4 (TA800598)• 1 vial of 20ug myc-DDK tagged CCDC93 HEK293T over-expression lysate lyophilized in RIPA buffer (LC412751). (Reconstitute into 20ul of 1x SDS sample buffer before loading; load 5ul per lane as WB control or as desired)
Amount:	100ul
Immunogen:	Human recombinant protein fragment corresponding to amino acids 293-631 of human CCDC93 (NP_061917) produced in E.coli.
Host:	Mouse
Isotype:	IgG1
Species Reactivity:	Human , Dog , Rat , Monkey
Guaranteed Applications:	WB
Suggested Dilutions:	WB 1:2000,
Concentration:	1.00 mg/ml
Buffer:	PBS (PH 7.3) containing 1% BSA, 50% glycerol and 0.02% sodium azide.
Purification:	Purified from mouse ascites fluids by affinity chromatography
Storage Condition:	Shipped at -20C. Upon delivery store at -20C. Dilute in PBS (pH7.3) if necessary. Stable for 12 months from date of receipt. Avoid repeated freeze-thaws.


Target

Target Name:	Homo sapiens coiled-coil domain containing 93 (CCDC93)
Alternative Name:	FLJ10996; FLJ25197; MGC13033
Database Link:	NP_061917
Function:	

This product is to be used for laboratory only. Not for diagnostic or therapeutic use.

© 2014 OriGene Technologies, Inc. 9620 Medical Center Dr., Suite 200, Rockville, MD 20850

Validation Data



HEK293T cells were transfected with the pCMV6-ENTRY control (Left lane) or pCMV6-ENTRY CCDC93 (RC206101, Right lane) cDNA for 48 hrs and lysed. Equivalent amounts of cell lysates (5 ug per lane) were separated by SDS-PAGE and immunoblotted with anti-CCDC93.

Western blot analysis of extracts (35ug) from 9 different cell lines by using anti-CCDC93 monoclonal antibody (HepG2: human; HeLa: human; SVT2: mouse; A549: human; COS7: monkey; Jurkat: human; MDCK: canine; PC12: rat; MCF7: human).

* More validation images may be available on our website: <http://www.origene.com/antibody/TA800598.aspx>